


# Ovation<sup>®</sup> by Essilor

Clearly Outstanding



**Minimum Suggested Fitting Height: 17MM**

## INSTRUCTIONS

### CENTERING:


- Mark/dot monocular PD & height on frame demo lenses
- Center frame on triangle with dots superimposed on "O" line
- Read R & L mono PD
- Read R & L mono height using lowest point of lower bevel

### SIZING:

Superimpose dot on fitting cross in lens diagram. The frame must fall within the diameter of the circle for the material required.

### VERIFICATION:

Upon receipt of glasses from the lab, check markings using the centering instructions to ensure proper measurements. If lenses are not marked, they must be remarked before verification.



©2005 Essilor of America, Inc. Airwear is a registered trademark of Essilor International, S.A. Ovation and Thin & Lite are registered trademarks of Essilor of America, Inc. Transitions is a registered trademark of Transitions Optical, Inc. L0W4200003 CP 01/05

